






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	"A"	"B"	WEIGHT
FLB12X15	1.93 (.49.0)	.54 (.13.7)	4.3 LB/10 PCS. (1960 G/10 PCS.)
FLB12X20	2.40 (.61.0)	.54 (.13.7)	4.7 LB/10 PCS. (2150 G/10 PCS.)
FLB58X15	1.93 (.49.0)	.65 (.16.5)	5.4 LB/10 PCS. (2470 G/10 PCS.)
FLB58X20	2.40 (.61.0)	.65 (.16.5)	5.7 LB/10 PCS. (2600 G/10 PCS.)



- NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 2. BRACKET ATTACHES TO 1 1/2" (38), 2" (50) LADDER RACK RAIL. BRACKET ACCEPTS 1/2" OR 5/8" THREADED ROD (NOT INCLUDED).
 3. THIS KIT CONTAINS ONE BRACKET, TWO 1/2" OR 5/8" HEX NUTS, AND ONE LOCKWASHER FOR ATTACHING TO LADDER RACK.
 4. DIMENSIONS IN PARENTHESES ARE IN METRIC.

CAD FILENAME/LAYERS										D35245BN_DC_FLB_02.PRT									
										PANDUIT CORP. TINLEY PARK, ILLINOIS									
										FIBER-DUCT LADDER RACK BRACKET KIT (FLB12X15, FLB12X20, FLB58X15, FLB58X20) CUSTOMER DRAWING									
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .04 (1.0) ANGLES ±									
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.									
										DRAWN BY TPC MAT'L: SCALE NONE									
										DATE 11-19-96 7 GAGE C.R.S.									
										CHECKED CEF DWG NO. 35245-14 DWG SIZE A									
										REV DATE BY CHK DESCRIPTION ECN R CUST SUP									
										D- REV'D NOTES 2 AND 3 TO REMOVE 12MM. C. REMOVED FLB12X15M AND FLB12X20M 35245-14									
										B- ADDED 12mm SIZE TO NOTES 2 AND 3. A. ADDED FLB12X15M AND FLB12X20M. 35245-14									
										RELEASED TO PRODUCTION 35245-14									
										2 1-24-00 JHN 1 1-28-99 DW HIW R 11-19-96 TPC CEF									