








COVER


NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBER-DUCT 4x4 OUTSIDE VERTICAL 45° ANGLE FITTING IS DESIGNED WITH A MINIMUM 2" (50.8) BEND RADIUS TO PROTECT FIBER OPTIC CABLES.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.

BASE



ENG. REF.: D35245BB_DC_FOV454X4_03.prt

CAD FILENAME/LAYERS



FOV454X4.pdf

PANDUIT CORP. TINLEY PARK, ILLINOIS

FIBER-DUCT 4x4 OUTSIDE VERTICAL 45° ANGLE FITTING (FOV454X4)

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
 (.X) ±
 (.XX) ±.03 (.8)

 (.XXX) ±
 ANGLES ±

 UNLESS OTHERWISE SPECIFIED,
 ALL DIMENSIONS ARE GIVEN IN
 INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

DW

DATE

10-9-95

CHK'D

CEF

MAT'L:

ABS

SCALE

NONE

DRAWING NO.

35245-02

DWG

A

SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	GMBH
-	-----	---	---	I. REVISED GENERAL NOTES. H. REVISED PART WEIGHT.	-----	--	--		
-	-----	---	---	G. REVISED MATERIAL. F. REVISED DRAWING TITLE.	-----	--	--		
4	12-15-06	MSO	RN	E. REVISED CAD FILENAME. D. REVISED AND REDRAWN.	34245-02	RN	RN		