

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
FR12ACB58	4.19LB/PC. (1898g/PC.)
FR12ACB58M	

**NOTES:**

- BRACKET ATTACHES TO NEW 5/8" OR 16mm THREADED ROD (NOT INCLUDED).
- THE FR12ACB58 & FR12ACB58M KIT INCLUDES:  
ONE (1) BRACKET SET (UPPER & LOWER ASSEMBLED),  
TWO (2) BRACKET CLIP ASSEMBLIES,  
TWO (2) 5/8" HELICAL SPRING LOCKWASHERS,  
TWO (2) 5/8-11 HEAVY HEX NUT (FR12ACB58 ONLY),  
TWO (2) M16X2 HEX NUT (FR12ACB58M ONLY).
- FINISH COLOR: BLACK
- DIMENSIONS IN PARENTHESIS ARE IN METRIC.



.65 DIA  
(16.5)



ENG. REF.: D37797ES\_DC\_FR12ACB58\_00A.prt

CAD FILENAME/LAYERS

37797-101.PDF

PANDUIT		CORP. TINLEY PARK, ILLINOIS	
FIBERRUNNER™ 12" ADJUSTABLE "C" BRACKET KIT (FR12ACB58, FR12ACB58M)		CUSTOMER DRAWING	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.XX) ±.03(1.8) ANGLES ± (.XX) ±.03(1.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY	JHNU	MAT'L	NONE
DATE	5-24-01		
CHECKED BY			
REV	R	DATE	5-24-01
BY	JHNU	DESCRIPTION	RELEASED TO PRODUCTION.
CHK		ECN	37797-101
CHK		CUST	
SUP			
DWG	37797-101		A
SIZE			