

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

△C

PANDUIT PART NUMBER	WEIGHT
FR12TB12 FR12TB12M	2.71 LB/EACH (1230g/EACH)



△H

△D

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE FIBERRUNNER 12x4 QUIKLOCK TRAPEZE BRACKET IS USED TO SUPPORT THE FIBERRUNNER 12x4 CABLE ROUTING SYSTEM BETWEEN TWO (2) SECTIONS OF NEW OR EXISTING 1/2" (M12) THREADED ROD THAT ARE 18" (457.2) - 20" (508) APART.
3. THE FIBERRUNNER 12x4 QUIKLOCK TRAPEZE BRACKET INCLUDES: ONE (1) BRACKET ASSEMBLY, FOUR (4) 1/2 HELICAL SPRING LOCKWASHERS, FOUR (4) 1/2-13 HEAVY HEX NUTS (FR12TB12 ONLY), FOUR (4) M12x1.75 HEX NUTS (FR12TB12M ONLY), ONE (1) 1/4-20 T-BOLT, ONE (1) 1/4-20 HEX KEPS NUT
4. FINISH COLOR: BLACK (EXCEPT FOR HARDWARE).
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.

△G



ENG. REF.: D38022CO_DC_FR12TB12_02.prt

CAD FILENAME/LAYERS

△A FR12TB12.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS
FIBERRUNNER 12x4 QUIKLOCK TRAPEZE BRACKET - 1/2" (M12) THREADED ROD (FR12TB12, FR12TB12M)
 CUSTOMER DRAWING △E △F

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 (.X) ± (.XXX) ±
 (.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: JHNU
 DATE: 10-2-01
 CHK'D: RPA

MAT'L: STEEL

SCALE: NONE
 DRAWING NO.: 38022-49
 DWG SIZE: A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	GMBH
2	7-31-06	DTP	RN	H. REVISED PART WEIGHT. G. REVISED GENERAL NOTE #3.	38022-49	RN	RN		
-	-----	---	---	F. REMOVED ALL REFERENCES TO PART NUMBER FR12TB58M.	-----	--	--		
-	-----	---	---	E. REVISED ENTIRE DRAWING TO INCLUDE FR12TB12.	-----	--	--		
-	-----	---	---	D. REVISED GENERAL NOTES. C. REVISED CHART.	-----	--	--		
1	1-12-05	MSO	RPA	B. REVISED DRAWING TITLE. A. REVISED CAD FILENAME.	38022-49	RN	RN		
R	10-2-01	JHNU	RPA	RELEASED TO PRODUCTION	38022-49	HIW	HIW		