




PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
FRHC12**2 (SEE NOTE 1)	78.74 IN ±.18 IN (2000.0mm ±4.6mm)	8.33 LB (3778g)	1.27 LB/FT (18.9g/cm)
FRHC12**6 (SEE NOTE 1)	72.00 IN ±.18 IN (1828.8mm ±4.6mm)	7.62 LB (3456g)	1.27 LB/FT (18.9g/cm)

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



 ENG. REF.: D37689BE_DC_FRHC12_01.prt

\\FRHC12.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS
FIBERRUNNER 12x4 SNAP-ON HINGED
COVER (FRHC12**2, FRHC12**6)
CUSTOMER DRAWING

$$\begin{array}{l} (.X) \pm \\ (.XX) \pm .03 \quad (0.8) \end{array} \quad \begin{array}{l} (.XXX) \pm \\ \text{ANGLES} \pm \end{array}$$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

CHK'D	RCRO
-------	------

PVC

37689-06

DWG
A
SIZE

-	-----	---	---	F. RELOCATED DIMENSION	-----	---	---		
-	-----	---	---	E. REMOVED DIMENSIONS D. REVISED ENTIRE CHART	-----	---	---		
2	7-20-06	DTP	RN	C. REVISED CAD FILENAME B. REVISED DRAWING TITLE	37689-06	RN	RN		
1	6-20-01	JHNU	HIW	A. REVISED FILENAME: CONVERTED TO PDF FILE	37689-06	HIW	HIW		
R	10-5-00	JHNU	RCRO	RELEASED TO PRODUCTION	37689-06	HIW	HIW		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMB