





| PANDUIT<br>PART NUMBER | WEIGHT                       |
|------------------------|------------------------------|
| FRRMBNF58              | 6.40 LB/EACH<br>(2903g/EACH) |

**NOTES:**

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE FIBERRUNNER QUIKLOCK NETRACK AND NETFRAME RACK MOUNT BRACKET ALLOWS FOR 5/8" THREADED ROD (NOT INCLUDED) TO BE MOUNTED TO THE TOP OF A PANDUIT NETRACK AND/OR NETFRAME CABLE MANAGEMENT RACK. THE FIBERRUNNER QUIKLOCK NETRACK AND NETFRAME RACK MOUNT BRACKET ALSO ALLOWS FOR THE FIBERRUNNER 4x4, 6x4 AND 12x4 CABLE ROUTING SYSTEMS TO BE FLUSH MOUNTED DIRECTLY TO THE TOP OF THE BRACKET WHEN USED WITH THE FIBERRUNNER QUICK MOUNT CLIPS (FROMC-X, SOLD SEPERATELY).
3. THE FIBERRUNNER QUIKLOCK NETRACK AND NETFRAME RACK MOUNT BRACKET KIT INCLUDES:  
ONE (1) BRACKET,  
FOUR (4) 1/4-20x3/4 HEX HEAD CAP SCREWS,  
FOUR (4) 1/4 HELICAL SPRING LOCKWASHERS,  
ONE (1) 5/8-11 HEAVY HEX NUT,  
ONE (1) 5/8 HELICAL SPRING LOCKWASHER.
4. FINISH COLOR: BLACK (EXCEPT FOR HARDWARE).
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D37797EX\_DC\_FRRMBNF58\_02.prt

CAD FILENAME/LAYERS

FRRMBNF58.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS

FIBERRUNNER QUIKLOCK NETRACK AND NETFRAME  
RACK MOUNT BRACKET - 5/8" THREADED ROD  
(FRRMBNF58)  
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:

(.X) ± (.XXX) ±  
(.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN IN  
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
MSO

DATE  
11-19-01

CHK'D  
RPA

MAT'L:

STEEL

SCALE NONE

DRAWING NO.  
37797-107DWG  
A  
SIZE

| REV | DATE     | BY  | CHK  | DESCRIPTION                                            | ECN       | R   | CUST | SUP | GMBH |
|-----|----------|-----|------|--------------------------------------------------------|-----------|-----|------|-----|------|
| 3   | 7-25-06  | DTP | RN   | G. REVISED PART WEIGHT                                 | 37797-107 | RN  | RN   |     |      |
| -   | -----    | --- | ---- | F. REVISED DIMENSION.                                  | -----     | --  | --   |     |      |
| -   | -----    | --- | ---- | E. REVISED PART GEOMETRY.<br>D. REVISED GENERAL NOTES. | -----     | --  | --   |     |      |
| 2   | 10-5-05  | MSO | DJWA | C. REVISED DRAWING TITLE.<br>B. REVISED CAD FILENAME.  | 37797-107 | RN  | RN   |     |      |
| 1   | 4-29-02  | MSO | RPA  | A. REVISED MAT'L REFERENCE<br>IN TITLE BLOCK.          | 37797-107 | HIW | HIW  |     |      |
| R   | 11-19-01 | MSO | RPA  | RELEASED TO PRODUCTION                                 | 37797-107 | HIW | HIW  |     |      |