





PANDUIT PART NUMBER	WEIGHT
FRTR4X4	0.38 LB/EACH (173g/EACH)



- NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER 4x4 3-SIDED BEND RADIUS CONTROL TRUMPET IS DESIGNED WITH A MINIMUM 2" (50.8) BEND RADIUS TO PROTECT FIBER OPTIC CABLES.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.

ENG. REF.: D37847BC_DC_FRTR4X4_01.prt

CAD_FILENAME/LAYERS

△ FRTR4X4.pdf

PANDUIT CORP. TINLEY PARK, ILLINOIS
FIBERRUNNER 4x4 3-SIDED BEND
RADIUS CONTROL TRUMPET (FRTR4X4)
A CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±	(.XXX) ±
(.XX) ± .03 (.8)	ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES. THIRD ANGLE PROJECTION.

DRAWN BY	JHNU
----------	------

DATE	7-18-01
------	---------

	CHK'D	RPA
--	-------	-----

	MAT'L:
--	--------

ABS

SCALE	NONE
-------	------

DRAWING NO.
37847-67

DWG
A
SIZE

-	-----	---	---	F. REMOVED DIMENSIONS E. RELOCATED DIMENSIONS	-----	--	--		
-	-----	---	---	D. REVISED PART WEIGHT C. REVISED GENERAL NOTES	-----	--	--		
1	7-14-06	DTP	RN	B. REVISED CAD FILENAME A. REVISED DRAWING TITLE	37847-67	RN	RN		
R	7-18-01	JHNU	RPA	RELEASED TO PRODUCTION	37847-67	HIW	HIW		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMB