



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
H2X2**2 (SEE NOTE 1)	78.74 IN ±.18 IN (2000.0mm ±4.6mm)	1.97 LB (894g)	0.30 LB/FT (4.5g/cm)
H2X2**6 (SEE NOTE 1)	72.00 IN ±.18 IN (1828.8mm ±4.6mm)	1.80 LB (816g)	0.30 LB/FT (4.5g/cm)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D38258CJ_DC_H2X2_00.prt

CAD_FILENAME/LAYERS

H2X2.pdf

PANDUIT CORP. TINLEY PARK, ILLINOIS
FIBERRUNNER 2x2 HINGED SLOTTED
CHANNEL (H2X2**2, H2X2**6)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±	(.XXX) ±
(.XX) ±.03 (0.8)	ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY	MSO
DATE	1-8-07
CHK'D	BN

MAT'L:	
--------	--

PVC

SCALE	NONE
-------	------

DRAWING NO.
38258 - 25

DWG
A
SIZE

R	1-8-07	MSO	RN	RELEASED TO PRODUCTION	38258-25	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	GMBH	