



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CPG**	.34 LB/10 PCS (152 g/10 PCS)

- NOTES:
- **1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 2. TWO (2) #6-32 X 1/4" SLOTTED OVAL HEAD SCREWS ARE INCLUDED WITH THIS PART.
 3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
 4. PART ACCEPTS 3 TYPES OF GFCI MODULE FRAMES, CFG1, CFG2, AND CFG4.



CAD FILENAME/LAYERS		MO0122BA_DC_00A.PRT	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
DESIGNER SERIES "GFCI"		FACEPLATE (CPG**)	
CUSTOMER DRAWING		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.010(.3) (.XX) ±.031(.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY	RCA	MAT'L:	NONE
DATE	08-22-97	ABS	
CHECKED BY			
REV	DATE	BY	CHK
R	08-22-97	RCA	
RELEASED TO PRODUCTION.			
ECN	00122-02	CHK	SUP
DESCRIPTION			
00122-02			
A			