





PANDUIT
PART NUMBER

WEIGHT

FR6TB38
FR6TB38M1.10 LB/EACH
(501g/EACH)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE FIBERRUNNER 4x4 AND 6x4 QUIKLOCK TRAPEZE BRACKET IS USED TO SUPPORT THE FIBERRUNNER 4x4 AND/OR 6x4 CABLE ROUTING SYSTEMS BETWEEN TWO (2) SECTIONS OF NEW OR EXISTING 3/8" (M10) THREADED ROD THAT ARE 10" (254) - 13" (330.2) APART.
3. THE FIBERRUNNER 4x4 AND 6x4 QUIKLOCK TRAPEZE BRACKET INCLUDES:
ONE (1) BRACKET ASSEMBLY,
FOUR (4) 3/8 HELICAL SPRING LOCKWASHERS (FR6TB38 ONLY),
FOUR (4) 3/8-16 HEAVY HEX NUTS (FR6TB38 ONLY),
FOUR (4) M10 HELICAL SPRING LOCKWASHERS (FR6TB38M ONLY),
FOUR (4) M10x1.5 HEX NUTS (FR6TB38M ONLY).
4. FINISH COLOR: BLACK (EXCEPT FOR HARDWARE).
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D38022CM_DC_FR6TB38_02.prt

CAD FILENAME/LAYERS



FR6TB38.pdf

-	-----	---	---	1. REVISED GENERAL NOTES.	-----	--	--		
2	7-31-06	DTP	RN	H. REVISED PART WEIGHT. G. REVISED DRAWING TITLE.	38022-47	RN	RN		
-	-----	---	---	F. REMOVED ALL REFERENCES TO PART NUMBER FR6TB12M.	-----	--	--		
-	-----	---	---	E. REVISED ENTIRE DRAWING TO INCLUDE P/N FR6TB38.	-----	--	--		
-	-----	---	---	D. REVISED GENERAL NOTES. C. REVISED CHART.	-----	--	--		
1	12-22-04	MSO	RPA	B. REVISED DRAWING TITLE. A. REVISED CAD FILENAME.	38022-47	RN	RN		
R	10-2-01	JHNU	RPA	RELEASED TO PRODUCTION	38022-47	HIW	HIW		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMBH

PANDUIT CORP		TINLEY PARK, ILLINOIS	
FIBERRUNNER 4x4 AND 6x4 QUIKLOCK TRAPEZE BRACKET - 3/8" (M10) THREADED ROD (FR6TB38, FR6TB38M)		CUSTOMER DRAWING	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± .03 (.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY JHNU	MAT'L:	SCALE NONE	
DATE 10-2-01	STEEL	DRAWING NO. 38022-47	DWG A
CHK'D RPA		SIZE	