



4.05 TYP.
[102.9]





1.10 TYP.
[28.1]

.97 TYP.
[24.7]



.64 —
[16.1]

$$\begin{array}{r} .40 \\ \overline{)10.3} \end{array}$$


PANDUIT P/N	WEIGHT
CRFX5	.59 LB/ 10PCS. (268g/ 10PCS.)

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESIS ARE IN METRIC.

										CAD FILENAME/LAYERS		D37523BE_DC_CRFX5_00A.PRT					
										PANDUIT CORP. TINLEY PARK, ILLINOIS							
										POWER LATCHING LDP5 CROSS (CRFX5) CUSTOMER DRAWING							
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ±.03(.8) ANGLES ±				UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
										DRAWN BY	MAT'L; ABS		SCALE		NONE		
R	09-28-00	JHNU	PM	RELEASED TO PRODUCTION			37523-05	HIW	HIW				DATE	09-28-00		DRAWING NO.	DWG
REV	DATE	BY	CHK	DESCRIPTION			ECN	-	R	CUST			SUP		CHK'D	PM	37523-05