


**NOTES:**

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. FOLLOWING PARTS INCLUDED IN ACCESSORY KIT:
  - ONE (1) BEND RADIUS CONTROL RAMP,
  - TWO (2) #10-32 x 1/2 MACHINE SCREWS,
  - ONE (1) END CAP,
  - ONE (1) VELCRO PAD,
  - ONE (1) BRACKET "T" BAR,
  - ONE (1) THUMB SCREW,
  - TWO (2) CEILING TRIM PLATES.
3. DIMENSIONS IN PARENTHESIS ARE IN METRIC.
4. ALL DIMENSIONS ARE REFERENCE DIMENSIONS.

|             |                             |
|-------------|-----------------------------|
| PANDUIT P/N | WEIGHT                      |
| PCPA11R20   | 16 LB/EACH<br>(7272 g/EACH) |

CROSS-SECTION  
OF POLE



2.90  
[73.6]

→ 1.77 ←  
[45.0]

$$\begin{array}{r} 22.50 \\ [571.5] \end{array} \xrightarrow{\quad \triangle \quad} \begin{array}{r} 15.50 \\ [393.7] \end{array}$$

— 4.50 TYP.   
[114.3]

11'-0"  
(3352)

CAD FILENAME/LAYERS

D37043BH\_DC\_PCPA11R20\_00B.prt

# PANDUIT

CORP. TINLEY PARK, ILLINOIS

PAN-WAY PAN-POLE (11 FT)  
(PCPA11R20)  
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± (.XXX) ±  
(.XX) ±.03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY MSC

|      |        |
|------|--------|
| 1.00 | MAT'L: |
|------|--------|

|       |      |
|-------|------|
| SCALE | NONE |
|-------|------|

|      |          |
|------|----------|
| DATE | 12 18 00 |
|------|----------|

## ALUMINUM

DRAWING NO.

37043-08

DWG

517

|          |          |            |            |                        |          |            |            |     |  |
|----------|----------|------------|------------|------------------------|----------|------------|------------|-----|--|
| <b>I</b> | 06-16-03 | <b>JBN</b> | RMHI       | A. ADDED DIMENSIONS    | 37043-08 | RGRO       | RGRO       |     |  |
| <b>R</b> | 12-18-00 | <b>MSO</b> | <b>CVV</b> | RELEASED TO PRODUCTION | 37043-08 | <b>HIW</b> | <b>HIW</b> |     |  |
| REV      | DATE     | BY         | CHK        | DESCRIPTION            | ECN      | CHK        | CUST       | SUP |  |