



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
UIT70FH4	.07 LB/PC (35 g/PC)
OF70FH4	

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. THE UIT70FH4 ACCEPTS FOUR (4) MINI-COM MODULES.
3. DIMENSIONS IN PARENTHESIS ARE IN METRIC.
4. THE UIT70FH4 FACEPLATE CAN BE USED WITH PANDUIT SURFACE RACEWAY SYSTEMS AND BOXES THAT ACCEPT 70mm SNAP-ON FACEPLATES (INCLUDES: T-70, TWIN-70, TE70, TG-70, ETC.)
5. POCKET TO BE USED WITH PANDUIT PART NUMBER UILC1**.
6. POCKET TO BE USED WITH PANDUIT PART NUMBER UILC4**.
7. POCKETS TO BE USED WITH PANDUIT PART NUMBER UIC1B**, UIC1P**, OR UIC1D**.
8. THE OF70FH4 CAN BE USED WITH OFFICE FURNITURE DESK MOUNT BOX (OFR20DMB).



CAD FILENAME/LAYERS		D38316BA_DC_UIT70FH4_01B.prt											
<h1>PANDUIT</h1> CORP TINLEY PARK, ILLINOIS ULTIMATE I.D. FOUR MINI-COM MODULE HORIZONTAL SLOPED SNAP-ON FACEPLATE (UIT70FH4 & OF70FH4) CUSTOMER DRAWING		UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± .03(.8) ANGLES ±											
		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.											
2	04-23-03	JBN	PM	D. ADDED NOTE 8 C. ADDED PART NUMBER OF70FH4	38316-06	RGRO	RGRO	DRAWN BY	MSO	MAT'L:	PVC	SCALE	NONE
1	07-09-02	JHEP	RGRO	B. REVISED NOTE 5 A. REVISED MODEL	38316-06	RGRO		DATE	12-06-01			DRAWING NO.	38316-06
R	12-06-01	MSO	CEO	RELEASED TO PRODUCTION	38316-06	RGRO		CHK'D	CEO			DWG	A
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	GMBH		SIZE	A