


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	LENGTH	WEIGHT
T70C**6	72.00 ±.13 (1829 ±3.0)	.9 LB/72 IN (409 G/1829 mm)
T70C**8	96.00 ±.13 (2438 ±3.0)	1.2 LB/96 IN (545 G/2438 mm)
T70C**10	120.00 ±.13 (3048 ±3.0)	1.5 LB/120 IN (682 G/3048 mm)
T70C**2 (SEE NOTE 5)	2000 mm ±3.0)	.98 LB/78.7 IN (447 G/2000 mm)

△ A
△ A
△ A
△ C

- NOTES:
- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 - THE T70C IS USED WITH THE T70B, T702B, AND TG70B.
 - DIMENSIONS IN PARENTHESES ARE IN METRIC.
 - USE TWO (2) FEET OF T70C (COVER) FOR EVERY ONE (1) FOOT OF T702B (BASE).
 - ONLY AVAILABLE OUTSIDE NORTH AMERICA.



CAD FILENAME/LAYERS D35541CA_DC-T70C-03A.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

T70 RACEWAY COVER
(T70C**6, T70C**8, T70C**10, T70C**2) △ G
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .010(.3)
(.XX) ± .031(.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

SCALE NONE

DRAWN BY JBA MAT'L: PVC

DATE 09-19-96

CEK

DRAWING NO. 35541-27

SIZE A

REV DATE BY CHK ECN DESCRIPTION

35541-27

35541-27

A

4 05-18-04 JBN BKR

35541-27

35541-27

3 04-14-00 MSO CAZ

35541-27

35541-27

2 10-20-98 DW HIW

35541-27

35541-27

1 07-08-98 DW HIW

35541-27

35541-27

R 09-19-96 JBA CEF

35541-27

35541-27

REV DATE BY CHK ECN DESCRIPTION

RELEASED TO PRODUCTION

RELEASED TO PRODUCTION