



+

PANDUIT PART NO.	WEIGHT
WCM35TR5	.243 LBS (110.22 G)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THIS PRODUCT IS INTENDED TO ROUTE CABLES BETWEEN PANDUIT WCM35 RACEWAY AND PANDUIT LD5, LDS5 OR LDP5 RACEWAYS.
3. THIS PRODUCT IS FEATURED WITH A 1" BEND RADIUS.
4. DIMENSIONS IN PARENTHESIS ARE IN METRIC.
5. NOMINAL WALL THICKNESS FOR COVER IS .100" [2.54].
6. NOMINAL WALL THICKNESS FOR INSERT AND BASE IS .075" [1.91]



										CAD FILENAME/LAYER		D38646BK_DC_WCM35TR5_00C.PRT		
										PANDUIT CORP. TINLEY PARK, ILLINOIS				
										3.5 INCH COVE MOLDING LOW PROFILE TRANSITION FITTING (WCM35TR5)				
										CUSTOMER DRAWING				
-	-----	---	---	RELEASED TO PRODUCTION		-----	----	----		UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .015 [.38] (.XX) ± .03 [.8] ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
2	12-31-03	JBN	BKR	C. REVISED DIMENSION TO REFERENCE		38646-07	RGRO	RGRO		DRAWN BY JBN DATE 08-13-03 CHK'D BKR	MAT'L: PVC	SCALE NONE		
1	12-08-03	JBN	BKR	B. REVISED DESCRIPTION IN TITLE BLOCK A. REVISED NOTE 2								DRAWING NO. 38646-07		DWG A
R	08-13-03	JBN	BKR	DRAWING RELEASED										
REV	DATE	BY	CHK	DESCRIPTION		ECN	CHK	CUST	SUP					

+