



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CPG**-2G	.494 LB/10 PCS (224.7 g/10 PCS)

NOTES:

- **1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. FOUR (4) #6-32 X 1/4" SLOTTED OVAL HEAD SCREWS ARE INCLUDED WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART ACCEPTS TWO (2) OF THE 3 TYPES OF GFCI MODULE FRAMES, CFG1, CFG2, AND CFG4.



											PANDUIT CORP. TINLEY PARK, ILLINOIS				
											CLASSIC SERIES "GFCI" DOUBLE A GANG FACEPLATE (CPG**-2G) CUSTOMER DRAWING				
											UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010(.3) (.XX) ±.03(.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
I	06-28-99	DW	HIW	A. REVISED TITLE NAME	00123-02	HIW	HIW				DRAWN BY RCA	MAT'L: ABS	SCALE NONE		
R	08-29-97	RCA	CEF	RELEASED TO PRODUCTION	00123-02	CEF	CEF				DATE 08-29-97		DRAWING NO. 00123-02		DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP			CHECKED BY CEF		SIZE		