



PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
S2X2**2 (SEE NOTE 1)	78.74 IN ±.18 IN (2000.0mm ±4.6mm)	1.84 LB (835g)	0.28 LB/FT (4.2g/cm)
S2X2**6 (SEE NOTE 1)	72.00 IN ±.18 IN (1828.8mm ±4.6mm)	1.68 LB (762g)	0.28 LB/FT (4.2g/cm)
S2X2**2NM (SEE NOTE 1)	78.74 IN ±.18 IN (2000.0mm ±4.6mm)	2.08 LB (943g)	0.29 LB/FT (4.4g/cm)
S2X2**6NM (SEE NOTE 1)	72.00 IN ±.18 IN (1828.8mm ±4.6mm)	1.74 LB (789g)	0.29 LB/FT (4.4g/cm)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



MOUNTING HOLES - BOTTOM VIEW
(S2X2**2 AND S2X2**6 ONLY)



ENG. REF.: D35245C0_DC_S2X2_00.prt

CAD_FILENAME/LAYERS

S2X2.pdf

PANDUIT CORP. TINLEY PARK, ILLINOIS

FIBER-DUCT 2x2 SOLID WALL CHANNEL
(S2X2**2, S2X2**6, S2X2**2NM, S2X2**6NM)

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±	(.XXX) ±
(.XX) ±.03 (0.8)	ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY	
----------	--

MAT'L:	
--------	--

SCALE

NONE

DATE

DRAWING NO.

DWG

CHK'D	
-------	--

RN

35245 - 41

SIZE

R	1-5-07	MSO	RN	RELEASED TO PRODUCTION	35245-41	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	GMBH	