





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

1.50 R REF
[38.1]



2.42
[61.5]



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.

PANDUIT PART NUMBER	WEIGHT
GRBRC4PG	0.59 LB/EA (268g/EA)

ENG. REF.: D39065JZ_DC/00 GRBRC4

CAD FILENAME/LAYERS

GRBRC4PG.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS
GRIDRUNNER BEND RADIUS CONTROL
- 4" DEEP BASKET (GRBRC4PG)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .05 (.XXX) ± .005
(.XX) ± .05 (1.3) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: MSO
DATE: 10-30-07
CHK'D: SABR

MAT'L: PRE-GALVANIZED
STEEL

SCALE: NONE
DRAWING NO.: 39065-73
DWG SIZE: A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	GMBH
R	10-30-07	MSO	SABR	RELEASED TO PRODUCTION	39065-73	RN	RN		