




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	WEIGHT
CRTB	7.57 LB/EA (3431g/EA)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE NET-ACCESS OVERHEAD CABLE ROUTING TRAPEZE BRACKET INCLUDES:
 - TWO (2) UPRIGHT BRACKET ASSEMBLIES,
 - ONE (1) TRAPEZE BAR ASSEMBLY,
 - TWO (2) 1/4-20x5/8 HEX HEAD CAP SCREWS,
 - TWO (2) 1/4 HELICAL SPRING LOCKWASHERS,
 - TWO (2) 1/4 SAE FLAT WASHERS
3. FINISH COLOR: BLACK (EXCEPT FOR HARDWARE)
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D39503CN_DC/00 CRTB

CAD FILENAME/LAYERS		CRTB.pdf	
PANDUIT		CORP TINLEY PARK, ILLINOIS	
NET-ACCESS OVERHEAD CABLE ROUTING TRAPEZE BRACKET (CRTB) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± .03 (.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY MSO	MAT'L:	SCALE NONE	
DATE 1-10-08	STEEL	DRAWING NO. 39503-17	DWG A
CHK'D SL			SIZE