



PANDUIT PART NUMBER	WEIGHT
FR12ACB58 FR12ACB58M	4.41 LB/EACH (1998g/EACH)



**NOTES:**

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
- THE FIBERRUNNER 12x4 QUIKLOCK ADJUSTABLE "C" BRACKET IS USED TO SUPPORT THE FIBERRUNNER 12x4 CABLE ROUTING SYSTEM FROM A SECTION OF NEW 5/8" (M16) THREADED ROD (NOT INCLUDED) OR CAN BE DIRECTLY MOUNTED TO THE CEILING.
- THE FIBERRUNNER 12x4 QUIKLOCK ADJUSTABLE "C" BRACKET INCLUDES:  
 ONE (1) BRACKET ASSEMBLY,  
 TWO (2) 5/8-11 HEAVY HEX NUTS (FR12ACB58 ONLY),  
 TWO (2) M16x2 HEX NUTS (FR12ACB58M ONLY),  
 TWO (2) 5/8 HELICAL SPRING LOCKWASHERS,  
 ONE (1) 1/4-20 T-BOLT,  
 ONE (1) 1/4-20 HEX KEPS LOCK NUT
- FINISH COLOR: BLACK (EXCEPT HARDWARE)
- DIMENSIONS IN PARENTHESES ARE IN METRIC.

ENG. REF.: D37797ES\_DC\_FR12ACB58\_01.prt

CAD FILENAME/LAYERS **FR12ACB58.pdf**

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	GMBH
-	-----	---	--	E. REVISED GENERAL NOTES.	-----	--	--		
-	-----	---	--	D. REVISED PART WEIGHT. C. REVISED DRAWING TITLE.	-----	--	--		
1	1-3-07	MSO	RN	B. REVISED CAD FILENAME. A. REVISED AND REDRAWN.	37797-101	RN	RN		

**PANDUIT** CORP TINLEY PARK, ILLINOIS

FIBERRUNNER 12x4 QUIKLOCK  
 ADJUSTABLE "C" BRACKET - 5/8" (M16)  
 THREADED ROD (FR12ACB58, FR12ACB58M)  
 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,  
 DIMENSIONAL TOLERANCES ARE:  
 (.X) ± (.XXX) ±  
 (.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
 ALL DIMENSIONS ARE GIVEN IN  
 INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: JHNU  
 DATE: 5-24-01  
 CHECK'D: HIW

MAT'L: STEEL

SCALE: NONE

DRAWING NO.: 37797-101  
 DWG SIZE: A