


PANDUIT PART NUMBER	WIRE RANGE	COLOR CODE	DIMENSIONS in.	
			A $\pm .03$	B
DV10-250M	12-10	YELLOW	0.98 (24.9)	.235 (5.97)

NOTES :

- USE FOR:
 - STRANDED COPPER WIRE ONLY
 - 194°F (90°C) MAX TEMP RATING OF INSULATION MATERIAL
 - 600V MAX VOLTAGE RATING
- MATERIAL :
 - STAMPING - .032" THK COPPER,NICKEL PLATED
 - HOUSING - VINYL
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- INSTALLATION TOOLS : CT-100, CT-260, CT-550
- PKG QTY. -L=50
-D=500
- WIRE STRIP LENGTH: $9/32^{+1/32}_{-0}$ (7.1 $^{+.8}_{-0}$)



A41195_05

05	11/04	KLFU		ADDED #10				 TINLEY PARK, ILLINOIS
04	1/01	KMDSKB		CAD FILE SPEC. WAS N41195AA_PCD_03	8938	JAC	CCH	
03	10/98	JD		MATERIAL WAS TIN PLATED	07642			
02	6/95	MS	LM	UPDATED NOTES AND DIMENSIONS	03404	LA	DH	
REV	DATE	BY	CHK	DESCRIPTION	ECN#	CUST	ENR	DRAWN BY FES
								CHK'D SCALE NONE
								DRAWING NO. A41195

2PC. VINYL INSULATED,
12-10, 250 X .032 MALE TAB