


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A ^{±.02}	W ^{±.01}	C ^{±.02}	M ^{±.02}	H ^{±.01}
P10-6RHT6	#6	.78 (19.81)	.31 (7.87)	.35 (8.89)	.62 (15.75)	.15 (3.81)
P10-8RHT6	#8	.78 (19.81)	.31 (7.87)	.35 (8.89)	.62 (15.75)	.17 (4.32)
P10-10RHT6	#10	.81 (20.57)	.38 (9.65)	.33 (8.38)	.62 (15.75)	.20 (5.08)
P10-14RHT6	1/4"	.96 (24.38)	.53 (13.46)	.42 (10.67)	.70 (17.78)	.27 (6.86)

NOTES:

1. RECOMMENDED FOR:
 - A. #12-10 AWG SOLID OR STRANDED
COPPER WIRE *
 - B. 650° F (343° C) MAX. TEMP. RATING
2. MATERIAL:
 - A. STAMPING- .04" (1.02) THK COPPER,
NICKEL PLATED
3. PACKAGE QTY: STD. PKG. - L = 50
BULK PKG. - D = 500
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOLS:
 - A. PANDUIT APPROVED: CT-100, CT-200,
CT-160, CT-260, CT-570
CT-1570

• APPROVED FOR USE WITH # 14 - 10 AWG SOLID OR STRANDED
COPPER WIRE WHEN INSTALLED WITH THE CT-570 OR CT-1570 TOOLS



A41267_01

									PANDUIT CORP. TINLEY PARK, ILLINOIS			
01	1/01	RM		FILESPEC WAS N41267AA_PCD_00					#12-10 BARREL NON-INSULATED RING TONGUE, HIGH TEMPERATURE, 650° F			
00	1/96	ED		REV.S TON NOTES & DIM.S/ FILESPEC WAS: A41267A	03883							
REV	DATE	BY	CHK	DESCRIPTION	ECN#	CUST	PM	APP	DRAWN BY	CHK'D	SCALE	DRAWING NO.
									EJD		NONE	A41267