


PANDUIT PART NUMBER	WIRE SIZE	DIMENSIONS in.			
		$\pm .03$ A	$\pm .01$ B DIA.	$\pm .01$ C DIA.	$\pm .03$ D
BSN22	26-22	.79 (20.1)	.08 (2.0)	.04 (1.0)	.47 (1.2)

NOTES:

- RATED FOR:
 - #26-22 AWG SOLID OR STRANDED COPPER WIRE
 - 221° F (105° C) MAX. TEMP. RATING
- MATERIAL:
 - .02 (0.5) THK COPPER, TIN PLATED
 - HOUSING - NYLON, YELLOW
- See www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- INSTALLATION TOOLS: CT-520
- WIRE STRIP LENGTH: $1/4 \text{ }^{+1/32}_{-0}$



WIRE STOP



05	04/11	SB		ADDED NOTE #3 FOR PACKAGE QTY				PANDUIT CORP. TINLEY PARK, ILLINOIS #26-22 BARREL NYLON INSULATED BUTT SPLICE
04	10/05	RT	LA	REMOVED UL & CSA NOTE	TR00036			
03	1/01	RM		FILESPEC WAS N41337AA_PCD_02				
02	7/95	MC		UPDATED NOTES AND DIMENSIONS	03438			
REV	DATE	BY	CHK	DESCRIPTION	ECN #			DRAWN BY: DAW CHK'D: SCALE: N/A DRAWING NO.: A41337