



NOTES:



- UL LISTED AND CSA CERTIFIED FOR:
 - 600V MAX VOLTAGE RATING
 - 221° F (105 C) MAX TEMP. RATING (CSA)
 - 257° F (125°C) MAX TEMP. RATING (UL)
 - STRANDED COPPER WIRE ONLY.
- MATERIAL:
 - STAMPING- BRASS, NICKEL PLATED
- COPPER, NICKEL PLATED
(FOR DNF10-250F1MB)
 - HOUSING-TYPE 6/6 NYLON
- DIMENSIONS IN BRACKETS ARE IN mm OR mm²
- COLORS ARE TRANSLUCENT
- SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- WIRE STRIP LENGTH: $9/32^{+1/32}_{-0}$ (7.1^{+0.8}₋₀)
 $3/8^{+1/32}_{-0}$ (9.5^{+0.8}₋₀)
(FOR DNF10-250F1MB)



LISTED
20H3
E78522



CERTIFIED
LR31212

PART NUMBER	TAB SIZE	WIRE RANGE AWG (mm ²)	COLOR (note 4)	MAX. INSUL.	DIMENSIONS in			CRIMP TOOLS
					A ±.03	B ±.01	C ±.01	
DNF18-250F1MB	.250 X .032 (6,3 X 0,8)	22-18 (1,5-1,0)	RED	.136 (3,45)	.91 (23,1)	.45 (11,4)	.34 (8,6)	CT-600-A CT-520 CT-1525 CT-2500
DNF14-250F1MB	.250 X .032 (6,3 X 0,8)	16-14 (1,5-2,5)	BLUE	.160 (4,06)	.91 (23,1)	.45 (11,4)	.34 (8,6)	
DNF10-250F1MB	.250 X .032 (6,3 X 0,8)	12-10 (4,0-6,0)	YELLOW	.220 (5,59)	.96 (24,4)	.45 (11,4)	.36 (9,1)	CT-600-A CT-1550 CT-1551 CT-2500

PANDUIT CORP.

TINLEY PARK, ILLINOIS

13 8/11 SHOR MODIFIED NOTE #5, ADDED INSTALLATION TOOLS

12 07/10 SRB Corrected tab size for DNF10-250F1MB

LOOSE PC. FULLY INSULATED UNI-MALE DISCONNECT
.250 X .032

REV DATE BY DESCRIPTION

DRAWN BY JV

CHK'D

SCALE

DRAWING NO.

A41402