



PART NUMBER		TAB SIZE	WIRE RANGE mm <sup>2</sup>	DIMENSIONS mm		
PREFIX	PK			A ±,38	B ±,25	C ±,25
DMNF6-63M	-L -D	6,3 X 0,8 (.250 X .032)	4,0-6,0 (12-10)	23,6 (.93)	6,4 (.25)	0,8 (.03)

## NOTES:

- USED FOR:
  - 600V MAX. VOLTAGE RATING.
  - 105° C (221°F) MAX. TEMP. RATING
  - STRANDED COPPER WIRE ONLY.
- PACKAGE QTY:
  - STD: L=50
  - BULK: D=500
- MATERIAL:
  - STAMPING: ETP 110 COPPER, TIN PLATED
  - HOUSING: TYPE 6/6 NYLON, YELLOW
- WIRE STRIP LENGTH: 7,1  $\begin{smallmatrix} +,8 \\ -0 \end{smallmatrix}$  (9/32  $\begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$ )
- DIMENSIONS IN BRACKETS ARE IN INCHES OR AWG.
- INSTALLATION TOOLS: REF. DWGS.  
A414522, A41523, A41524, A41525



A41510\_04

04	11/04	KLFU		ADDED LOGO AND MARKING 6,0 WIRE RANGE 4,0 WAS 2,5; B DIM WAS 6,30 C DIM WAS 0,76				 <b>PANDUIT CORP.</b> <span>TINLEY PARK, ILLINOIS</span>			
03	10/97	TM	WJB	CHANGED DECIMAL POINTS TO COMMAS	06432	LA	DH				
02	1/92	BK	RS	NOTES: ADDED #6, ADDED COPPER TO #1C. CHANGED COMMAS TO PERIODS	00765	LA	KS				
01	8/91	SJ	SJ	WIRE STRIP LENGTH WAS 8,7 mm	00563	LA	KS				
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY JMV	CHK'D LM	SCALE NONE	DRAWING NO./CAD FILENAME A41510

2,5 - 6,0 mm<sup>2</sup>; 6,3 TAB  
METRIC 3PC. BARREL INSULATED MALE DISCONNECT