

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER		TAB SIZE	WIRE RANGE AWG (mm ²)	DIMENSIONS		HOUSING COLOR	TOOL CHART RECOMMENDED PRESSES CP-861, CP-860 CP-851, CP-862 CA-800/CA9 DIE INSERTS	
PREF I X	PK			A ^{±.030}	B ^{MAX}			
DNF 18-250M	-3K	.250 X .032 (6.3 X 0.8)	22-18 (0.5-1.0)	.90 (22.9)	.145 (3.68)	RED		CD-800-1 CA9-1A
DNF 14-250M	-3K	.250 X .032 (6.3 X 0.8)	16-14 (1.5-2.5)	.90 (22.9)	.162 (4.11)	BLUE		CD-800-2 CA9-2A
DNF 10-250M	-2K	.250 X .032 (6.3 X 0.8)	12-10 (4.0-6.0)	.95 (24.1)	.225 (5.72)	YELLOW	CD-800-3 CA9-3B	


NOTES:

1. USED FOR:
 - A. 600V MAX. VOLTAGE RATING.
 - B. 105° C (221°F) MAX. TEMP. RATING
 - C. STRANDED COPPER WIRE ONLY.
 2. PACKAGE QTY:
 - 3K = 3000 PC. REEL
 - 2K = 2000 PC. REEL
 3. MATERIAL:
 - A. STAMPING: COPPER, NICKEL PLATED
 - B. HOUSING: TYPE 6/6 NYLON
 4. WIRE STRIP LENGTH: $9/32 \begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$ (7.1 $\begin{smallmatrix} +.8 \\ -.0 \end{smallmatrix}$) (DNF18-250M & DNF14-250M)

 $: 11/32 \begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$ (8.7 $\begin{smallmatrix} +.8 \\ -.0 \end{smallmatrix}$) (DNF10-250M)
 5. DIMENSIONS IN BRACKETS ARE IN mm OR mm².
- 



CERTIFIED
LR31212



					PANDUIT CORP. TINLEY PARK, ILLINOIS
06	9/10	SRB	SRB	Removed CSA exception for DNF10-250M	REELSMART™, DISCO™, NYLON BARREL INSULATED MALE DISCONNECTS (.250 X .032 TAB SIZE)
REV	DATE	BY	CHK	DESCRIPTION	DRAWN BY BDK CHK'D RLS SCALE NONE DRAWING NO./CAD FILENAME A41533