

1. RECOMMENDED TOOLS: CP-860, CP-861, CP-851, CP-862
2. APPLICATOR: CA-800 , CA9 ,CA-800EZ
3. CRIMP DIE : CD800-9, CD9-9C
4. VOLTAGE RATING: 600 V MAX.
5. TEMPERATURE RATING: 105° C
6. PACKAGE QUANTITY 1500 PCS/REEL
7. DIMENSIONS ARE IN INCHES (MILLIMETERS)
8. BRASS THICKNESS .018 (.457) TIN PLATED
9. FOR STRANDED COPPER WIRE ONLY
10. HOUSING : TYPE 6/6 NYLON
11. CURL SLOTS: DNFR18205FIB-KD
DNFR18206FIB-KD, DNFR14205FIB-KD,
DNFR14206FIB-KD ONLY.

$$U_L$$


PART NUMBER	TAB SIZE	WIRE RANGE	COLOR	MAX. INSUL.	DIMENSIONS			
					A±.03 (.8)	W±.01 (.3)	X±.03 (.8)	F±.02 (.5)
DNFR18250FIB-KD	.250 X .032	22-18	RED	.178 (4.6)	.57 (14.48)	.37 (9.40)	.60 (15.24)	.21 (5.33)
DNFR18205FIB-KD	.205/.187 X .032	22-18	RED	.178 (4.6)	.57 (14.48)	.37 (9.40)	.60 (15.24)	.21 (5.33)
DNFR18206FIB-KD	.205/.187 X .020	22-18	RED	.178 (4.6)	.57 (14.48)	.37 (9.40)	.60 (15.24)	.21 (5.33)
DNFR14250FIB-KD	.250 X .032	16-14	BLUE	.178 (4.6)	.57 (14.48)	.37 (9.40)	.60 (15.24)	.21 (5.33)
DNFR14205FIB-KD	.205/.187 X .032	16-14	BLUE	.178 (4.6)	.57 (14.48)	.37 (9.40)	.60 (15.24)	.21 (5.33)
DNFR14206FIB-KD	.205/.187 X .020	16-14	BLUE	.178 (4.6)	.57 (14.48)	.37 (9.40)	.60 (15.24)	.21 (5.33)

A41124_09

								 CORP. TINLEY PARK, ILLINOIS			
								DISCO-RIGHT ANGLE FULLY INSULATED FEMALE DISCONNECTS .250 X .032, .205/.187 X .032/.020			
09	04/14/05	FS		Tolerance of "F" was $\pm .01$ ($\pm .3$)							
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	APP	DRAWN BY	CHK'D	SCALE	DRAWING NO./CAD FILENAME
								MG		NONE	A41124