





NOTES:

- UL LISTED AND CSA CERTIFIED FOR:
 - 600V MAX VOLTAGE RATING
 - 221°F (105°C) MAX TEMP RATING
 - STRANDED COPPER WIRE ONLY
 - 6-12 LBS INITIAL INSERTION/WITHDRAWAL FORCE
- PACKAGE QTY:-2K=2000 PIECES
CONTINUOUS MOLDED STRIP CARRIER
- MATERIAL:
 - STAMPING-CDA 260 BRASS, TIN PLATED
 - HOUSING-TYPE 66 NYLON
- DIMENSIONS IN BRACKETS ARE IN mm OR mm²
- COLORS ARE TRANSLUCENT



LISTED
20H3
E78522



CERTIFIED
LR31212

TOOL CHART - RECOMMENDED
PRESSES:CP-851,CP-860,CP-861, CP-862

PART NUMBER	TAB SIZE	WIRE RANGE AWG (mm ²)	COLOR (note 5)	MAX. INSUL.	DIMENSIONS in.			CA-800/CA9 APPLICATOR DIES
					A ±.03	B ±.02	C ±.02	
DNF18250F1BX-2K	.250 X .032 (6.3 X 0.8)	22-18 (0.5-1.5)	RED	.210 (5.33)	.93 (23.6)	.35 (8.9)	.22 (5.5)	CD-800-6 CD9-6B
DNF18205F1BX-2K	.205/.187 X .032 (5.2/4.8 X 0.8)	22-18 (0.5-1.5)	RED	.210 (5.33)	.87 (22.1)	.31 (7.9)	.22 (5.5)	
DNF18206F1BX-2K	.205/.187 X .020 (5.2/4.8 X 0.5)	22-18 (0.5-1.5)	RED	.210 (5.33)	.87 (22.1)	.31 (7.9)	.22 (5.5)	
DNF14250F1BX-2K	.250 X .032 (6.3 X 0.8)	16-14 (1.5-2.5)	BLUE	.240 (6.09)	.93 (23.6)	.35 (8.9)	.22 (5.5)	CD-800-8 CD9-8B
DNF14205F1BX-2K	.205/.187 X .032 (5.2/4.8 X 0.8)	16-14 (1.5-2.5)	BLUE	.240 (6.09)	.87 (22.1)	.31 (7.9)	.22 (5.5)	
DNF14206F1BX-2K	.205/.187 X .020 (5.2/4.8 X 0.5)	16-14 (1.5-2.5)	BLUE	.240 (6.09)	.87 (22.1)	.31 (7.9)	.22 (5.5)	

A41167_04

04	7/03	KLFU		ADD INT. SERRATIONS AND RMVD SLOTS ADDED CP-862, CD9 & CA9 TO TOOL CHART				 PANDUIT CORP. TINLEY PARK, ILLINOIS
03	1/01	KMDSKB		CAD FILE SPEC. WAS N41167AA_PCD_02	8938	JAC	CCH	
02	1/95	MS		UPDATED NOTES AND DIMENSIONS	02946			
01	4/88	FS	LM	REVISED TO PREFERRED FORMAT		LA	KRS	DISCO-FEMALE DISCONNECTS EXPANDED FULLY INSULATED .250 X .032, .205/.187 X .032/.020
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY DSM CHK'D SCALE NONE DRAWING NO. A41167