


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. UL AND CSA LOGOS APPEAR ON ALL PARTS AS SHOWN.
2. 'PANDUIT' STAMPED ON ALL PARTS.
3. IF HEX SIZE IS NOT GIVEN, FLAT HEAD SCREW USED.
4. MATERIAL; COPPER
5. FOR USE WITH COPPER WIRE ONLY.
6.  NEMA HOLE SIZES AND SPACING.
7. ADDITIONAL MULTIPLE WIRE COMBINATIONS FOR CD35-36-Q ARE:

|              |                         |
|--------------|-------------------------|
| A. TWO-#10'S | D. ONE-#10 WITH ONE-#12 |
| B. TWO-#12'S | E. ONE-#12 WITH ONE-#14 |
| C. TWO-#14'S |                         |
8. THESE PARTS ARE ROHS COMPLIANT.

| PART<br>NUMBER | COPPER<br>CONDUCTOR<br>SIZE<br>RANGE | CURRENT<br>RATING<br>(AMPS) | BOLT<br>HOLE<br>SIZE | HEX<br>SIZE | Dimensions in inches |      |      |      |      |     | STD.<br>PKG.<br>QTY. | STD.<br>CTN.<br>QTY. |
|----------------|--------------------------------------|-----------------------------|----------------------|-------------|----------------------|------|------|------|------|-----|----------------------|----------------------|
|                |                                      |                             |                      |             | A                    | W    | G    | S    | C    | T   |                      |                      |
| CD35-36-QY     | #14-#6*                              | 50                          | 3/16'                | **          | 2.13                 | .38  | .22  | 1.00 | .38  | .07 | 25                   | 100                  |
| CD70-14-QY     | #12-#2                               | 90                          | 1/4'                 | **          | 2.26                 | .50  | .25  | 1.00 | .38  | .09 | 25                   | 100                  |
| CD125-14-QY    | #8-#2/0                              | 125                         | 1/4'                 | **          | 2.94                 | .62  | .44  | 1.00 | .44  | .13 | 25                   | 100                  |
| CD225-56-QY    | #6-#4/0                              | 225                         | 5/16'                | 5/8'        | 3.38                 | 1.00 | .50  | 1.00 | .63  | .13 | 25                   | 100                  |
| CD300-38-3Y    | #1-350                               | 300                         | 3/8'                 | 3/4'        | 4.94                 | 1.00 | .94  | 1.00 | 1.38 | .19 | 3                    | 12                   |
| CD400-38-3Y    | #1/0-500                             | 400                         | 3/8'                 | 3/4'        | 5.62                 | 1.50 | .94  | 1.75 | .88  | .19 | 3                    | 12                   |
| CD650-12-3Y    | 600-1000                             | 650                         | 1/2'                 | 1-1/8'      | 6.88                 | 2.00 | 1.19 | 1.75 | 1.75 | .25 | 3                    | 12                   |

\*And combinations

C41666\_00

|     |      |      |     |                                   |         |     |    |                                                                           |        |                                                                                         |                    |            |
|-----|------|------|-----|-----------------------------------|---------|-----|----|---------------------------------------------------------------------------|--------|-----------------------------------------------------------------------------------------|--------------------|------------|
|     |      |      |     |                                   |         |     |    | PANDUIT CORP. TINLEY PARK, ILLINOIS                                       |        |                                                                                         |                    |            |
|     |      |      |     |                                   |         |     |    | CD SERIES COPPER MECHANICAL LUGS CUSTOMER DRAWING                         |        |                                                                                         |                    |            |
|     |      |      |     |                                   |         |     |    | UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:                   |        | UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION. |                    |            |
|     |      |      |     |                                   |         |     |    | (.X) ±                    (.XXX) ±<br>(.XX) ±                    ANGLES ± |        |                                                                                         |                    |            |
|     |      |      |     |                                   |         |     |    | DRAWN BY JHNU                                                             | MAT'L: |                                                                                         | SCALE NONE         |            |
| 00  | 3/06 | JHNU | LEM | DRAWING RELEASED - ROHS COMPLIANT | PC00348 |     |    | DATE 3/06                                                                 | COPPER |                                                                                         | DRAWING NO. C41666 | DWG SIZE A |
| REV | DATE | BY   | CHK | DESCRIPTION                       | ECN #   | APP | PM | CHK'D                                                                     |        |                                                                                         |                    |            |