

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	250 STR/FLEX
Wire Type	Stranded Copper: Class G, H, I, K, M, Locomotive
Wire Strip Length	1-1/16 in.
Stud Size	3/8 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	YELLOW
Panduit Die Index No. on Barrel	P62
Alternate Industry Die Index No. () on Barrel	(16)



LISTED
Wire Connector



PANDUIT CORP. TINLEY PARK, ILLINOIS

LCDX250-38-X
Copper Lug - Two-Hole, Standard Flex Barrel

SCALE	N/A
--------------	-----

DRAWING NO / CAD FILE

LCDX250-38-CUST