



- CD-940 DIES TO BE USED WITH CT-940CH TOOL ONLY
- CD-920 DIES CAN BE USED WITH THE CT-940CH AND CT-2940 TOOLS WITH CD-940-DA DIE ADAPTER.

					CRIMP TOOL PART NUMBERS	
PANDUIT PART NUMBER	CONDUCTOR SIZE	A ±.08	D ±.010	E ±.010	CT-720	CT-820, CT-820H CT-730, CT-830H CT-940H CT-2920 CT-2940*
					DIE PART #/DIE SET COLOR/COD. CT CRIMPS	
SA300-2	300 MCM	3.12	1.01	.65	CD-720-6 BLUE P76 4 CRIMPS	CD-920-400 BLUE P78 2 CRIMPS
SA350-2	350 MCM	3.37	1.12	.72	CD-720-7 BROWN P87 4 CRIMPS	CD-920-500 BROWN P87 4 CRIMPS
SA400-2	400 MCM	3.75	1.19	.76		CD-920-600 GREEN P89 4 CRIMPS
SA500-2	500 MCM	3.87	1.32	.84		CD-920-500A PINK P98 4 CRIMPS
SA600-2	600 MCM	4.12	1.44	.92		CD-920-750 BLACK P106 4 CRIMPS
SA750-1	750 MCM	4.62	1.60	1.03		CD-940-750* RED P125 4 CRIMPS
SAB00-1	800 MCM	4.75	1.66	1.05		CD-940-800A* GRAY P140 4 CRIMPS
SA1000-1	1000 MCM	5.25	1.84	1.18		CD-940-1000A* BROWN P181 4 CRIMPS



1. MATERIAL: SEAMLESS ALUMINUM TUBING
2. TIN PLATED
3. BARREL CODED WITH DIE SET INDEX NUMBER
4. UL LISTED
5. CSA CERTIFIED
6. FOR STRANDED ALUMINUM AND COPPER WIRE
7. ALL DIMENSIONS ARE IN INCHES



LISTED



CERTIFIED

										C41219_01			
										PANDUIT CORP TINLEY PARK, ILLINOIS			
										SA SERIES ALUMINUM SPLICES 300 THRU 1000 MCM			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) 2 (.XXX) 2 (.XX) 2 ANGLES 2			
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION			
01	4/01	JAME		ADDED THE LETTER "P" TO ALL DTE NUMBERS. ADDED TOOL NO.CT-2940 TO TOOL TABLE AND TOOL NOTE**						DRAWN BY TSM	MAT'L:	SCALE NONE	
00	9/97	TM	RLS	DWG. RELEASED				06202	DH	LA	DATE 9/15/97	SEE NOTES	DRAWING NO. C41219
REV	DATE	BY	CHK	DESCRIPTION				ECN #	PM	CUST	CHK'D RLS		DWG B