





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	MAXIMUM BUNDLE DIAMETER	PKG QTY	"L" LENGTH +/- .3 [7]
MLT4DSH-Q316	4" [102]	25	29.5" [749]
MLT6DSH-Q316	6" [152]	25	41.5" [1054]
MLT8DSH-Q316	8" [203]	25	53.5" [1359]



SECTION A - A  
SCALE 4:1



BODY WRAPS AROUND BUNDLE TWO TIMES PASSING THROUGH THE HEAD TWICE (NOT TO SCALE)

- NOTES:
1. APPLICATION TOOL - RT2HT, RT2HTN
  2. MINIMUM LOOP TENSILE STRENGTH - 1200 LBS. (5340 NEWTONS) WHEN TESTED ON A 3" MANDREL.
  3. [ ] DENOTES DIMENSION IN MILLIMETERS
  4. MATERIAL: 316 STAINLESS STEEL
  5. GREEN COLOR STRIPE IDENTIFIER FOR DOUBLE WRAP PRODUCT

PANDUIT CORP. TINLEY PARK, ILLINOIS

METAL LOCKING TIE  
SUPER HEAVY-DUTY DOUBLE LOOP

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:  
(.XX) -+ .02 (.XXXX) -+ N/A  
(.XXX) -+ .010 ANGLES ± 2°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION
06A	09/09	MIM	CCH	REPLACED EASY-THREAD HEAD DESIGN WITH THE ORIGINAL CONVENTIONAL HEAD DESIGN

DRAWN BY MIM	MAT'L:  SEE NOTES	SCALE NTS
DATE 08/27/08		DRAWING NO. N41166BS_DC
CHK'D SKB		DWG SIZE A