



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	PACKAGE QTY.	MAX BUNDLE DIA	"LENGTH" ±.3 [ 7 ]
MLTFC2H-LP316	50	2" [ 51 ]	7.9" [ 201 ]
MLTFC2.7H-LP316	50	2.7" [ 69 ]	10.15" [ 258 ]
MLTFC4H-LP316	50	4" [ 102 ]	14.3" [ 362 ]
MLTFC6H-LP316	50	6" [ 152 ]	20.5" [ 521 ]
MLTFC8H-LP316	50	8" [ 203 ]	26.8" [ 679 ]



NOTES:

1. APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, HTMT OR ST3MT
2. MINIMUM LOOP TENSILE STRENGTH - 250 LBS. (1112 NEWTONS) WHEN TESTED ON A 1.5" MANDREL.
3. BRACKETS [ ] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:  
 .XXX = ±.010 [ .25 ]    .XX = ±.02 [ .5 ]  
 .X = ±.03 [ .8 ]        ANGLES = ±2°
5. MATERIAL: 316 STAINLESS STEEL
6. COATING - POLYESTER  
 COATING THICKNESS: .002 MIN./ .005 MAX. PER SIDE



03A	2/12	MIM	RGRO	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY			 CORP.                      TINLEY PARK, ILLINOIS METAL LOCKING TIE - COATED HEAVY SERIES 316 STAINLESS STEEL (CUSTOMER DRAWING)	
02	11/05	JMMR	EJD	Ⓐ ADDED MLTFC2.7H-LP316 TO TABLE	SS00112	---		---
01	3/05	JAMB	PAB	DRAWING REVISED TO REFLECT CURRENT COATED HEAVY SERIES PRODUCT	12501	CCH		JJB
00	11/04	JAMB	PAB	RELEASED	12169	CCH		JJB
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM		CUST
								DRAWN BY: JAMB    CHK'D: PAB    SCALE: 2x    DRAWING NO.: N41193BS_DC