



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	WIRE RANGE AWG (mm ²)	REEL QUANTITY	COLOR	STRIP LENGTH : 9/32" : 8.791	MAX. WIRE O.D.	DIM "L"	DIM "P"	OD-1	ID-1
FSD75-8-5K10	20 (0.50)	5000	WHITE*	13/32 (10)	.09 (2.4)	.57 (14.5)	.31 (8)	.05 (1.4)	.04 (1.0)
FS75-8-5K3	20 (0.50)	5000	ORANGE	13/32 (10)	.09 (2.4)	.57 (14.5)	.31 (8)	.05 (1.4)	.04 (1.0)
FSD76-8-5K8	18 (0.75)	5000	GRAY*	13/32 (10)	.10 (2.6)	.57 (14.5)	.31 (8)	.06 (1.6)	.05 (1.2)
FS76-8-5K10	18 (0.75)	5000	WHITE	13/32 (10)	.10 (2.6)	.57 (14.5)	.31 (8)	.06 (1.6)	.05 (1.2)
FS76-8-5K7	18 (0.75)	5000	LT. BLUE	13/32 (10)	.10 (2.6)	.57 (14.5)	.31 (8)	.06 (1.6)	.05 (1.2)
FSD77-8-5K2	18 (1.00)	5000	RED*	13/32 (10)	.11 (2.8)	.57 (14.5)	.31 (8)	.07 (1.8)	.06 (1.4)
FS77-8-5K4	18 (1.00)	5000	YELLOW	13/32 (10)	.11 (2.8)	.57 (14.5)	.31 (8)	.07 (1.8)	.06 (1.4)
FSD78-8-5K0	16 (1.50)	5000	BLACK*	13/32 (10)	.13 (3.3)	.57 (14.5)	.31 (8)	.08 (2.1)	.07 (1.7)
FS78-8-5K2	16 (1.50)	5000	RED	13/32 (10)	.13 (3.3)	.57 (14.5)	.31 (8)	.08 (2.1)	.07 (1.7)
FSD80-8-3K6	14 (2.50)	3000	BLUE*	13/32 (10)	.15 (3.9)	.57 (14.5)	.31 (8)	.10 (2.6)	.09 (2.2)
FS80-8-3K8	14 (2.50)	3000	GRAY	13/32 (10)	.15 (3.9)	.57 (14.5)	.31 (8)	.10 (2.6)	.09 (2.2)

*INSULATION COLOR CONFORMS TO DIN SPECIFICATION

NOTES:

- MATERIAL:
A. STAMPING - COPPER, TIN PLATED
B. HOUSING - POLYPROPYLENE, COLOR CODED
- DIMENSIONS IN BRACKETS ARE IN mm OR mm²
- FOR TOLERANCING REFER TO DIN 46228 PART 4
- PACKAGE QTY.: 5000 PC. SPOOL, 3000 PC. SPOOL (FSD-80 only)
- INSTALLATION TOOL: CA-10
CP-881



02	03/22	BDK	LCA	VMB	MODIFIED MAX. WIRE O.D. MODIFIED ID-1. ADDED INSTALLATION TOOL CP-881.	A41747
01	04/07	BCT	LCA	TRO	MODIFIED LENGTH TO 'L'; ADDED 'ID-1'; CHANGED FSD75 & FSD76 PART NUMBERS	TR00251
00	02/07	DAW	LCA	TRO	ADDED '-8-' TO P/N FOR LENGTH; REMOVED 'D' FROM NON-DIN COLORED PARTS	TR00208
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE		INSULATED FERRULES ON REEL	
CONTROL DRAWING			
ITEM REVISION NAME		N41737BA/02.PRT	
DATASET FILE NAME		N41737BA/02.PRT	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.X : .XXX : .XX : ANGLES :		N/A	
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
DAW		A41737	
DAW		SHT 1 OF 1	
01/07		A	