


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



SECTION "A-A"

PART NO.	MATERIAL	PKG. QTY.
MMP350H-C	304 S.S.	100
MMP350H-C316	316 S.S.	100
MMP350H-M	304 S.S.	1000
MMP350H-M316	316 S.S.	1000

NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS
2. CUSTOM PERMANENT MARKING AVAILABLE. CONSULT FACTORY.
3. USE WITH HEAVY CROSS SECTION MLT'S
4. TOLERANCE (UNLESS OTHERWISE SPECIFIED)
 .xxx = ±.020 (.51)
 .xx = ±.03 (.8)

08B	8/08	JAMB	SKB	ADDED PART NO'S.FOR BULK QTY 1000 MARKER PLATES		
08A	7/07	JAMB	SKB	REMOVED PART NO'S. MMP350W38-C & MMP350W38-C316 FROM PART TABLE. REMOVED FIGURE 2 & SECT."B-B"	-----	---
07	1/07	JAMB	SKB	ADDED MAT'L. THICKNESS DIM. TO SECTION "A-A" & "B-B"	---	SS00314 ---
06	11/06	JAMB	SKB	REVISED FIGURE 1 HEAVY MARKER PLT & ADDED FIGURE 2 STD. MARKER PLATE USED WITH STD.MLT CROSS SECTION	---	SS00287 ---
05	10/03	BRH	DPN	ADDED PACKAGE QTY./CODE TO PART NUMBERS IN TABLE	CCH	11167 JJB
04	2/01	KMD	JAC	FILE SPEC WAS N41046SA_PCD_03	TRO	09066 JAC
03	11/96	JKD	JD	ADDED NOTE 4	MS	05240 LCA
				MAT'L WAS 302/304		
				FOR MMP350H AND MMP350W38		
02	1/94	DL	SM	ADDED SLOTS TO PART	GP	02045 LA
REV	DATE	BY	CHK	DESCRIPTION	PM	ECN CUST

N41046BS_DC/08B

PANDUIT

CORP. TINLEY PARK, ILLINOIS

METAL MARKER PLATE-HEAVY
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
 (.X) ± (.XXX) ±
 (.XX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION

DRAWN BY SAM

MAT'L

SCALE FULL & NOTED

DATE 2/4/91

STAINLESS STEEL

DRAWING NO. N41046BS_DC

CHK'D JAC

DWG.
A
SIZE