




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
FSTMA**	1.00 lb/100 PCS 1454.54g/100 PCS



ST CONNECTOR WITH 3mm BOOT  
(DUSTCAP REMOVED)

- NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
  2. ACCEPTS 62.5/125 AND 50/125um MULTIMODE GLASS OPTICAL FIBER CABLE.
  3. MATERIALS:
    - CONNECTOR BODY/HARDWARE: NICKEL-PLATED ZINC BOOT: THERMOPLASTIC RUBBER
    - FERRULE: ZIRCONIA (CERAMIC)
  4. COMPLIES WITH THE FIBER OPTIC PERFORMANCE REQUIREMENTS AS SPECIFIED BY TIA/EIA-568-B.3
  5. COMPATIBLE WITH TIA-EIA-604-2 (FOCIS-2)
  6. FERRULE DIAMETER: 2.4985/2.4995mm.
  7. DIMENSIONS IN BRACKETS ARE METRIC (mm).
  8. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF ROHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTIONS OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE ROHS TECHNICAL ADAPTATION COMMITTEE.



ST CONNECTOR WITH 900um BOOT  
(DUSTCAP REMOVED)

ST SIMPLEX MULTIMODE CONNECTOR  
CUSTOMER DRAWING



**PANDUIT**  
CORP.  
TINLEY PARK, ILL 60477

ALL DIMENSIONS ARE GIVEN IN INCHES.  
DIMENSIONS SPECIFIED IN PARENT PARENTS ARE:  
(1.X) ANGLES  
(1.XXX) ANGLES  
(1.XXX) ANGLES  
DRAWING FILENAME  
MO1197BF\_DC\_01B.prt  
SCALE  
NONE  
PART NO.  
FSTMA\*\*  
DRAWING NO.  
01197-06  
SIZE  
A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	DATE	MMW	AS NOTED	01197-06	A
2	06-19-06	MC	CHK	RELEASED TO PRODUCTION	01197-06					12-03-01	MMW			

[illegible][illegible]

**PANDUIT**™  
CORP.  
TINLEY PARK, ILL. 60477

**MIT**  
CORP.  
TEL 60477

DRAWING FILENAME	MO1197BF_DC-01B.prt
SCALE	NONE
PART NO.	

DRAWING NO.		FSTMA**	
01197-06 SHEET 2		SIZE A	