



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
T70PGS	.49 LB/10 PCS (221 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. TWO (2) #6-32 X 1/4" SLOTTED OVAL HEAD SCREW IS INCLUDED WITH THIS FACEPLATE.
3. THE T70PGS FACEPLATE CAN BE USED WITH PANDUIT SURFACE RACEWAY SYSTEMS AND BOXES THAT ACCEPT 70mm SNAP-ON FACEPLATES (INCLUDES: T-70, TWIN-70, TE70, TG-70, ETC.)
4. THE T70PGS FACEPLATE ACCEPTS PANDUIT ONE, TWO, AND FOUR POSITION RECTANGULAR (GFCI) MODULE FRAMES - CFG1, CFG2, CFG4 (OR RECTANGULAR COMMUNICATION MODULE FRAMES OF MOST OTHER MANUFACTURERS)
5. THE T70PGS FACEPLATE IS NOT INTENDED FOR USE WITH ELECTRICAL DEVICES.
6. DIMENSIONS IN PARENTHESES ARE IN METRIC.



[69.8]										[0.7]										CAD FILENAME/LAYERS D37239BA_DC_T70PGS_00B.PRT									
																				PANDUIT CORP. TINLEY PARK, ILLINOIS									
																				T-70 SINGLE GANG RECTANGULAR COMMUNICATION SNAP-ON FACEPLATE (WITH SCREW HOLES TO MOUNT A MODULE FRAME) CUSTOMER DRAWING									
																				UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) : .005 (.XX) ± .010 ANGLES : 1° ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.									
I	3-6-00	MISO																		DRAWN BY PM MAT'L: SCALE NONE									
R	9-27-99	PM	HIW																	DATE 9-27-99 PVC DRAWING NO. 37239-03 DWG A									
																				CHK'D CHW HIW									
REV	DATE	BY	CHK	DESCRIPTION										ECN		-	R	CUST	SUP										