


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



CAD FILENAME/LAYERS

M00800AA_DC_05A.PRT

PANDUIT

CORP. TINLEY PARK, ILLINOIS

MINI-COM 2 POSITION
SHUTTERED BOX (CBXS2C**)

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .03 (.8) ANGLES ±
(.XXX) ± .010 (.3)
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY	JSP	MAT'L	NONE
DATE	12-5-00		
CHECKED BY			

ABS

DRAWING NO.
00800-14
SHEET 2 OF 2


DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
R	12-5-00	JSP		SEE SHEET 1 OF 2	00800-14			

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CBXS2**-A	.53 LB/10 PCS (242.5 g/10 PCS)

- NOTES:**
- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 - SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
 - DIMENSIONS IN PARENTHESES ARE IN METRIC.
 - ALSO INCLUDED WITH BOX:
 - (2) PLTIM-M PAN-TY
 - (1) STRIP OF 1.00" X .75" FOAM TAPE FOR MOUNTING
 - BASE HAS 1 POCKET FOR OPTIONAL MAGNET (CSBM-X)
 - BREAKOUTS DESIGNED TO ACCEPT LD5/LDPS TRACEWAY. (DOES NOT ENTER BOX.)



NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE, AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

CAD FILENAME=LAYERS

M00800AA_DC_05A.PRT

PANDUIT

CORP. TINLEY PARK, ILLINOIS

MINI-COM 2 POSITION
SHUTTERED BOX (CBXS2**-A)

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .010 (.3)
(.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JSP
DATE 12-5-00
CHECKED BY

MAT'L:

SCALE

NONE

ECN

00800-14

RELEASED TO PRODUCTION.

DESCRIPTION

BY CHK

CHK

CUST

SUP

BOX: ABS
DOORS: HIPS

DRAWING NO.

00800-14

SHEET 1 OF 2

DWG

A

SIZE