





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT P/N	WEIGHT
CFPHSL4**	.57 LB/10 PCS. (256.7 G/10 PCS.)

NOTES:

- **1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. PART INCLUDES:
 - 1- FACEPLATE
 - 2- MOUNTING SCREWS
 - 1- LABEL
 - 1- LABEL COVER
4. DIMENSIONS IN PARENTHESIS ARE IN METRIC.



MODEL FILENAME		SIZE
DRAWING FILENAME	M00734BC_DC/05A	A
4 POSITION MINI-COM HORIZONTAL SLOPED FACEPLATE W/LABEL COVERS CUSTOMER DRAWING		
PANDUIT [®] TINLEY PARK, IL 60487		I.I. NUMBER
		PRODUCT SPEC/ PKG SPEC
 ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010(.3) (.XX) ±.03(.8) ANGLES ±		ASSY METHOD/ TEST METHOD
DRAWN BY JsP		SCALE NONE
DATE 10-5-99		PART NO. CFPHSL4**
CHK'D MECA		DRAWING NO. 00734-11
REVIEW DRAWING NUMBERS		
MAT'L ABS		

1	5-9-11	BJN	JSP	A. UPDATED MODEL TO REV 05 MADE VIEWS HORIZONTAL	00734-11		JSP		
R	10-5-99	JsP	MECA	RELEASED TO PRODUCTION	00734-11				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH