



PANDUIT P/N	WEIGHT
UICFPSE4**	.70 LB/10 PCS (318.0 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- FACEPLATE
 - 1- CLEAR SCREW COVER
 - 1- COLOR COORDINATED SCREW COVER
 - 2- CLEAR LABEL COVER
 - 2- MOUNTING SCREW



MODEL FILENAME		M01288BB_UICFPSE4_04.PRT		SIZE A
DRAWING FILENAME		M01288BB_DC_04A.PRT		
MINI-COM™ ULTIMATE ID™ 4 POSITION VERTICAL SLOPED EXECUTIVE SERIES FACEPLATE CUSTOMER DRAWING				
 PANDUIT ™ TINLEY PARK, ILL 60477		1.1. NUMBER N/A		
 THIRD ANGLE PROJECTION JsP		PRODUCT SPEC N/A		
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ±.03(.8) ANGLES ±		WORK INSTRUCTION N/A		
DRAWN BY JsP		SCALE NONE		
DATE 7-24-02		PART NO. UICFPSE4**		
CHK'D		DRAWING NO. 01288-07		
		MATERIAL: ABS		

