



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




FRONT VIEW
SHOWN W/O DUSTCAPS

PANDUIT P/N	DESCRIPTION
FCXO-24-10Y	OPTIMIZED 50/125 10GbE MULTIMODE 24 FIBER, MTP TO LC CASSETTE MODULE
FCX-24-10Y	50/125 10GbE MULTIMODE 24 FIBER, MTP TO LC CASSETTE MODULE
FCZO-24-10Y	OPTIMIZED 50/125 10GbE OM4 MULTIMODE 24 FIBER, MTP TO LC CASSETTE MODULE
FCZ-24-10Y	50/125 10GbE OM4 MULTIMODE 24 FIBER, MTP TO LC CASSETTE MODULE
FC6-24-10Y	62.5/125 MULTIMODE 24 FIBER, MTP TO LC CASSETTE MODULE
FC5-24-10Y	50/125 MULTIMODE 24 FIBER, MTP TO LC CASSETTE MODULE
FC9-24-10Y	9/125 SINGLEMODE 24 FIBER, MTP TO LC CASSETTE MODULE


NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. MATERIALS:
A. BOX AND LID: POWDER COATED ALUMINUM
B. ADAPTER: COMPOSITE PLASTIC
4. CASSETTE MODULE WEIGHT: 7.25oz (205.6g)
5. DIMENSIONS IN BRACKETS ARE METRIC.




PORT DESIGNATIONS

AS VIEWED FROM THE FRONT
WITH THE ADAPTERS REMOVED FOR CLARITY



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	DATE	CHK'D	DESCRIPTION	PART NO.	DRAWING NO.	SIZE
02	09-17-09	EFK		RELEASED TO PRODUCTION	02068-36					10/26/04	MTV	FIBER OPTIC CASSETTE MODULE 24 FIBER MTP TO DUPLEX LC CONFIGURATION CUSTOMER DRAWING	SEE TABLE	02068-36	A



PANDUIT™
CORP.
TINLEY PARK, ILL 60477

DRAWING FILENAME
MO2068AA_DC/00G

SCALE
NONE

PART NO.
SEE TABLE

DRAWING NO.
02068-36

SIZE
A

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.

DIMENSIONAL TOLERANCES ARE:
(.X) ±.010 (0.3)
(.XX) ±.03 (0.8) ANGLES

THIRD ANGLE PROJECTION

DRAWN BY: MC REVIEW DRAWING NUMBERS