



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



**FRONT VIEW**

SHOWN W/O DUSTCAPS




**PORT DESIGNATIONS**

AS VIEWED FROM THE FRONT WITH THE ADAPTERS REMOVED FOR CLARITY

PANDUIT P/N	DESCRIPTION
FCX0-12-10Y	OPTIMIZED 50/125 10GbE MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FCX-12-10Y	50/125 10GbE MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FCZ0-12-10Y	OPTIMIZED 50/125 10GbE OM4 MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FCZ-12-10Y	50/125 10GbE OM4 MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FC6-12-10Y	62.5/125 MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FC5-12-10Y	50/125 MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FC9-12-10Y	9/125 SINGLEMODE 12 FIBER, MTP TO LC CASSETTE MODULE

**NOTES:**

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. MATERIALS:  
A. MODULE HOUSING AND COVER: PLASTIC  
B. ADAPTER: COMPOSITE PLASTIC
4. CASSETTE MODULE WEIGHT: 3.82oz (108.2g)
5. DIMENSIONS IN BRACKETS ARE METRIC.




REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	DATE	CHK'D	PART NO.	DRAWING NO.	SIZE
												SEE TABLE	02068-45	A
02	09-17-09	EFK		RELEASED TO PRODUCTION	02068-45					01-18-05	MTV	SEE TABLE	02068-45	A

FIBER OPTIC CASSETTE MODULE 12 FIBER  
MTP TO DUPLEX LC CONFIGURATION  
CUSTOMER DRAWING



**PANDUIT**™  
CORP.  
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.  
DIMENSIONAL TOLERANCES ARE:  
(.X) ±.010 (0.3)  
(.XX) ±.03 (0.8) ANGLES

DRAWING FILENAME: MO2068AL\_DC/00E  
SCALE: NONE

DRAWN BY: MC  
DATE: 01-18-05  
CHK'D: MTV

REVIEW DRAWING NUMBERS

PART NO.: SEE TABLE  
DRAWING NO.: 02068-45  
SIZE: A