



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




FRONT VIEW
SHOWN W/O DUSTCAPS

PANDUIT P/N	DESCRIPTION
FCX-12-3SY	50/125 10GbE OM3 MULTIMODE 12 FIBER, MTP TO SC CASSETTE MODULE
FC6-12-3SY	62.5/125 OM1 MULTIMODE 12 FIBER, MTP TO SC CASSETTE MODULE
FC5-12-3SY	50/125 MULTIMODE OM2 12 FIBER, MTP TO SC CASSETTE MODULE
FC9-12-3SY	9/125 OS1 SINGLEMODE 12 FIBER, MTP TO SC CASSETTE MODULE
FC9-12-3AS	9/125 OS1 SINGLEMODE 12 FIBER, MTP TO SC/APC CASSETTE MODULE

NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- MATERIALS:
A. BOX AND LID: POWDER COATED ALUMINUM
B. ADAPTER: COMPOSITE PLASTIC
- CASSETTE MODULE WEIGHT: 7.88oz (223.5g)
- DIMENSIONS IN BRACKETS ARE METRIC.



										FIBER OPTIC CASSETTE MODULE 12 FIBER, MTP TO 12-SIMPLEX SC CONFIGURATION CUSTOMER DRAWING	
										 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	
										ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±.010 (0.3) (.XX) ±.03 (0.8) ANGLES	
										DRAWING FILENAME M02068AB_DC-Y_00C.prnt	
										SCALE NONE	
										PART NO. SEE TABLE	
										DRAWING NO. 02068-47	
										SIZE A	
R	12-15-06	MC		RELEASED TO PRODUCTION	02068-47					DATE 10/26/04	
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH	CHK'D