




PANDUIT P/N	WEIGHT
UICMPPA48BLY	.91 LB/EACH PC (412.3 g/EACH PC)



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- METAL STAMPING
 - 12- 4 POSITION FACEPLATE WITH
1 LABEL POCKET
(ASSEMBLED TO METAL STAMPING)
 - 12- CLEAR LABEL COVER
 - 1- SCREW KIT (INCLUDES FOUR
#12-24 SCREWS)
 - 1- SCREW KIT (INCLUDES FOUR
M6 SCREWS)
5. LABELS SOLD SEPARATELY.



NETWORK SYSTEMS
MAY 26 2006
ENGINEERING DEPT



MODEL FILENAME		MO1207AG_UICMPA48BL_03.PRT		SIZE		A	
DRAWING FILENAME		MO2479AT_DC20_00A.PRT					
MINI-COM ULTIMATE ID ANGLED 48 PORT MODULAR PATCH PANEL WITH 1 LABEL POCKET PER FACEPLATE CUSTOMER DRAWING							
		PANDUIT ™ CORP. TINLEY PARK, ILL 60477		1:1. NUMBER		N/A	
				PRODUCT SPEC		N/A	
 THIRD ANGLE PROJECTION		ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.XX) ± (.XXX) ± (.010(.3)) (.XX) ± (.03(.8)) ANGLES ±		WORK INSTRUCTION		N/A	
				SCALE		NONE	
DRAWN BY JsP		MATERIAL: PANEL - CRS FACEPLATE - ABS		PART NO. UICMPA48BLY			
DATE 4-19-06				DRAWING NO. 02479-020			
CHK'D 