




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CP24BLY	3.91 LB/10 PCS (1773.5 g/10 PCS)

NOTES:

- NOTES:
1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
 2. THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
 3. PACKAGE CONTENTS:
 - i- 24 PORT STAMPING
 - i- SCREW KIT (INCLUDES FOUR #12-24 SCREWS AND 4 LOCK WASHERS)
 - i- SCREW KIT (INCLUDES FOUR M6 SCREWS)
 - i- REMOVAL TOOL (CPT)
 4. PATCH PANELS ACCEPT SNAP-IN MINI-COM MODULES.
 5. DIMENSIONS IN PARENTHESIS ARE IN METRIC.



										MODEL FILENAME M02077AD_RCP24BL_00.PRT		SIZE A
										DRAWING FILENAME M02479CH_DC61_00B.PRT		
										MINI-COM 24 PORT ALL METAL MODULAR PATCH PANEL CUSTOMER DRAWING		
										 PANDUIT TM CORP. TINLEY PARK, ILL 60477		I.I. NUMBER N/A
										 THIRD ANGLE PROJECTION		PRODUCT SPEC N/A
										ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .03(.8) ANGLES ±		WORK INSTRUCTION N/A
										DRAWN BY JsP		SCALE NONE
										MATERIAL STAINLESS STEEL		PART NO. CP24BLY
										DATE 4-26-06		DRAWING NO. 02479-061
										CHK'D MJD		
REV	DATE	BY	CHK	DESCRIPTION			ECN	R	CUST	SUP	OTH	
I	6-16-06	JsP	MJD	A. ADDED GROUNDING STUD CALLOUTS.			02479-061					
R	4-26-06	JsP	MJD	RELEASED TO PRODUCTION			02479-061					