


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	LENGTH	WEIGHT
	*6" (152.41) / -2" (50.81)	
UTPCH6SL25Y	8' (2438.4)	1.20 LB/EACH (545 G/EACH)
UTPCH10SL25Y	10' (3048)	1.44 LB/EACH (654 G/EACH)
UTPCH15SL25Y	15' (4572)	2.05 LB/EACH (932 G/EACH)
UTPCH20SL25Y	20' (6096)	2.66 LB/EACH (1209 G/EACH)
UTPCH6SL25Y	6' (1829)	.96 LB/EACH (435 G/EACH)

- NOTES:
1. SEE CURRENT CATALOG TO INDICATE PACKAGE QUANTITY.
 2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
 3. MATES WITH FEMALE RJ21 CONNECTOR AND 10/100 BASE T PATCH PANEL.
 4. CATEGORY 5 AND POWER SUM RATED.
 5. DIMENSIONS IN PARENTHESES ARE IN METRIC.



CAD FILENAME/PLANS

MO2479KJ_DC271_00A.PRT

PANDUIT

CORP. TINLEY PARK, ILLINOIS
25 PAIR PATCH CORD ASSEMBLY
ONE 110° LEFT RJ21 MALE CONNECTOR
AND ONE 180° RJ21 MALE CONNECTOR
(UTPCH1X1SL25Y) CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.XX) ±.03(.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

NER

MAT'L:

DATE

3-20-06

CONNECTOR HSG:
UL94 V-0 THERMOPLASTIC
CABLE JACKET: PVC

DRAWING NO.

02479-271

NONE

DWG

A

REV

DATE

BY

CHK

DESCRIPTION

ECN

CHK

CUST

SUP

CHECKED BY

DATE

3-20-06

CONNECTOR HSG:
UL94 V-0 THERMOPLASTIC
CABLE JACKET: PVC

DRAWING NO.

02479-271

DWG

A