




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CPPA48HDVNSWBL	6.88 LB/10 PCS (3215.2.0 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
- THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- PACKAGE CONTENTS:
 - (1) -48 PORT ANGLED STAMPING
 - (6) -8 POSITION FACEPLATE (ASSEMBLED TO PANEL)
 - (1) -SCREW KIT (INCLUDES FOUR #12-24 SCREWS AND FOUR LOCK WASHERS)
 - (1) -SCREW KIT (INCLUDES FOUR M6 SCREWS)
- DIMENSIONS IN PARENTHESIS ARE IN METRIC.



MODEL FILENAME	M0074IAS_CPPA48HDVNSWBL_00.PRT	SIZE	A
DRAWING FILENAME	M0074IAS_DC_00B.PRT		

MINI-COM 48 PORT ANGLED HIGH DENSITY MODULAR PATCH PANEL WITH VERTICAL NUMBERING SEQUENCE CUSTOMER DRAWING

<p>PANDUITTM CORP. TINLEY PARK, ILL 60477</p>	I.I. NUMBER	N/A
	PRODUCT SPEC	N/A
<p>THIRD ANGLE PROJECTION</p>	WORK INSTRUCTION	N/A
	SCALE	NONE
DRAWN BY	DATE	PART NO.
JsP	5-26-06	CPPA48HDVNSWBL
DATE	CHK'D	DRAWING NO.
5-26-06	MJD	00741-95
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± .03 (.81) ANGLES ± .010 (.25) (.XX) ± .03 (.81) ANGLES ± .010 (.25)		MATERIAL: STAMPING: 18 GAGE C.R.S. FACEPLATE: ABS

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
I	9-28-06	JsP	MJD	A. CLARIFIED TITLE.	00741-95				
R	5-26-06	JsP	MJD	RELEASED TO PRODUCTION	00741-95	MJD	MJD		MJD