


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. 

PANDUIT PART NO.*	DESCRIPTION	WEIGHT
DP24584TV25Y	25 PAIR RJ21 CONNECTOR 24 PORT 100 BASE-T WIRED (WITH VELCRO)	0.90 LB (408g)

NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM AS WELL AS OPTIONAL SNAP-IN LABEL HOLDERS.
2. 24 PORT PATCH PANEL 2 PAIR WIRED (1,2,3,6). 8 POSITION MODULE JACK 4 POSITION WIRED.
3. THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
4. FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) M6X1X15MM METRIC SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.
6. MATERIALS- STAMPING: CRS  
RJ45 MODULE HOUSING: V-0 ABS



MOUNTS TO 19" UNIVERSAL RACKS

VELCRO STRAPS (12 PLACES)

MODEL FILENAME M02128AB-24P-100BT-ASSY-06.PRT	SIZE A
DRAWING FILENAME M02479JX-DC259-01A.PRT	
TITLE 24 PORT DATA-PATCH CATEGORY 5 100 BASE-T PATCH PANEL CUSTOMER DRAWING	

**PANDUIT CORP.**  
TINLEY PARK, ILL. 60477

ALL DIMENSIONS ARE IN INCHES.  
DIMENSIONAL TOLERANCES ARE:  
1.X) ±.13/3.31.XXX) ±.010  
1.XX) ±.03/8.1ANGLES ±1°

WORK INSTRUCTION  
SCALE  
NONE

DATE 3-20-06	REVISED 3-20-06	REVIEWER NER	PART NO. SEE CHART
-----------------	--------------------	-----------------	-----------------------

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	DATE	WJC
1	5-15-06	NER		E. WEIGHT WAS 1.02 LB. D. NOTE 6 HOUSING WAS POLYESTER. C. DIM. 3.73 WAS 3.72. B. DIM. 1.41 WAS 1.39. A. UPDATED MODEL.	02479-259						
R	3-20-06	NER	WJC	RELEASED TO PRODUCTION	02479-259		RMD				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	DATE	WJC