



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT
PART NO.


WEIGHT
(APPROX.)

DP246X88TGY

1.25 lb (567 g)

NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
2. MATERIAL:
PANEL HOUSING: STEEL
RJ45 MODULE: THERMOPLASTIC RESIN UL94V-0
PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
RETENTION CAP:
THERMOPLASTIC RESIN UL94V-0
3. 24 PORT PATCH PANEL 8 POSITION 8 WIRE.
4. THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
5. FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) METRIC M6x1x15MM SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
6. DIMENSIONS IN PARENTHESES ARE IN METRIC.
7. USE 110 STYLE TERMINATION TOOL FOR PUNCH DOWN.
8. RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.

MODEL FILENAME M02088AA_1RU_24PORT_PANEL_ASSY_04		SIZE A
DRAWING FILENAME M02479JB_DC238/00B		
TITLE DP6A 10GIG 24 PORT PATCH PANEL CUSTOMER DRAWING		
 PANDUIT ™ CORP. TINLEY PARK, IL 60477		I.I. NUMBER
		PRODUCT SPEC
		WORK INSTRUCTION
 THIRD ANGLE PROJECTION		SCALE .25:1
DRAWN BY LZ		PART NO. SEE CHART
DATE 3-4-06		DRAWING NO. 02479-238
CHK'D CEF		
REVIEW DRAWING NUMBERS		

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
1	12-2-08	BJN	EJH	A. DP6A 10GIG WAS DP6 10GIG™	02479-238				
R	3-4-06	LZ	CEF	RELEASED TO PRODUCTION	02479-238	CEF	CEF		CEF