



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



* PANDUIT P/N	WEIGHT
△ GPB24-X	.34 LB/ EACH (155.1 g/ EACH)

- NOTES:
- \* 1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
  3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
  4. MATERIAL:  
BASE - POLYCARBONATE  
WIRE STRIP- POLYCARBONATE



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01	5-8-00	LZ		A. P/N WAS GPB24 B. REMOVED NOTE 5.					
R	2-5-99	JSP	CEF	RELEASED TO PRODUCTION.					
					00340-14				
					00340-14	CEF			

MODEL FILENAME	M00340BK_DC_00B	SIZE	A
DRAWING FILENAME			
TITLE	GIGA-PUNCH™ BASE 24 PORT A (GPB24-X) CUSTOMER DRAWING		
<b>PANDUIT</b> <sup>®</sup> TINLEY PARK, IL 60477		I.I. NUMBER	
		PRODUCT SPEC	
		WORK INSTRUCTION	
		SCALE	NONE
		PART NO.	
		DRAWING NO.	00340-14

THIRD ANGLE PROJECTION	
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.	
DIMENSIONAL TOLERANCES ARE:	
(.X) ± (XXX) ±	
(.XX) ±	
ANGLES ±	
REVIEW DRAWING NUMBERS	
DRAWN BY	JSP
DATE	2-5-99
CHK'D	CEF